



DIVERSIFIED
TESTING LABORATORIES, INC.
 WORLDWIDE SERVICE

“We Test Per Your Request”

336 WEST FRONT STREET
 P.O. BOX 4004
 BURLINGTON, NORTH CAROLINA 27215
 PHONE (336) 227-7710 • FAX (336) 227-1175
 www.diversifiedtestinglabs.com

May 29, 2024

THORLABS LTD.
 204 Lancaster Way Business Park
 Ely, Cambridgeshire CB6 3NX
 United Kingdom

Reference: Laboratory Test Report
 Lab Identification No. 59873
 Invoice No. 91213

One (1) sample, identified as **R&DTABLES – Rubberized Thorlabs Protective Material**, was received and tested in accordance with the California Administrative Code Title 19--Public Safety, Section 1237.1 Flame Resistance, Small Scale Test. The results are as follows:

Test Results

Specimen Number	After Flame (sec)		Char Length (in)	
	<u>Length</u>	<u>Width</u>	<u>Length</u>	<u>Width</u>
1	0.0	0.0	1.2	1.8
2	0.0	0.0	1.9	1.5
3	0.0	0.0	1.8	1.6
4	0.0	0.0	1.3	1.5
5	<u>0.0</u>	<u>0.0</u>	1.4	1.5
Avg.	0.0	0.0		

The sample submitted, in its original state, **meets** the minimum requirements of the above standard. The char length may not exceed 6.0 inches for any individual specimen and the average afterflame time may not exceed 4.0 seconds in the length or width directions.

Sincerely,

Brian S. Dement

BSD/mr

