

# Scan Report

## Single Fiber - IEC PC 2.50 mm



FC-PC-16

Date & Time of Scan: Wed, Jul 11, 2018 11:19 AM

Connector ID:FC-PC-16

Product ID:sm fiber



**Result: PASS**

### PASS/FAIL MEASUREMENTS

Parameter	Min	Max	Value	Result
Radius of Curvature (mm)	5	30	8.905	Pass
Fiber Height (nm)	-229.869	100	79.232	Pass
Apex Offset (um)	0	70	32.594	Pass

### ADDITIONAL MEASUREMENTS

Parameter	Value
Apex Offset X (um)	25.307
Apex Offset Y (um)	-20.54

#### Norland Products

2540 ROUTE 130

Suite 100

Cranbury, NJ 08512 USA

Tel: (609) 395-1966

Fax: (609) 395-9006

[norlandproducts.com](http://norlandproducts.com)

Username:  
admin

Operator ID:  
Thorlabs

#### Sample Parameters

Sample Name:  
PC Connector

Product Type:  
Standard Connector

Fiber Diameter:  
126

Nominal Y-Angle:  
0

Ferrule Type:  
Ceramic