


Legacy 25-Pin D-Type Stepper Motor Cable

The PAA611 cable features a 25-pin male D-type connector on one end and a 15-pin female D-type connector on the other end. This cable can be used with the MST601, BSC001, BSC002, and BSC003 stepper motor controllers.



PAA611

| ITEM # | \$ | £ | € | RMB | DESCRIPTION |
|--------|----------|---------|---------|----------|---|
| PAA611 | \$ 61.80 | £ 44.50 | € 53.77 | ¥ 492.55 | Legacy APT Stepper Motor Drive Cable, 3.0 m |

Z8 DC Motor Extension Cable




PAA632

The PAA632 is an extension cable for use with the Z8 series actuators (page 608). This cable is 2.5 m (8.2') long with a 15-pin D-type male connector on one end and a female 15-pin D-type connector on the other end.

| ITEM # | \$ | £ | € | RMB | DESCRIPTION |
|--------|----------|---------|---------|----------|----------------------------------|
| PAA632 | \$ 52.80 | £ 38.02 | € 45.94 | ¥ 420.82 | Z8 Series Extension Cable, 2.5 m |

Laser Diode and Temperature Controller Cables and Connectors



CAB4001

CON4001

CAB420-15

These cables are the same cables included with many of our laser diode current and TEC controllers. The table below outlines the controller that each cable is typically used with. The CON series are connector kits only.

| ITEM # | USE | COMPATIBLE CONTROLLER |
|-----------|------------|---|
| CAB400 | LD | LDC200C Series, LDC8000, ITC8000 (LD) |
| CAB420-15 | TEC | TED200C, TTC001, TED8000, ITC8000 (TEC) |
| CAB430 | LD and TEC | ITC100 Series, ITC8000-DS15 |
| CAB530 | LD and TEC | ITC5022, ITC5052, ITC5102 |
| CAB4000 | TEC | TED4015, ITC4000 Series – 5 A (Max) |
| CAB4001 | TEC | TED4015, ITC4000 Series – 20 A (Max) |
| CAB4005 | LD | LDC4000 Series, ITC4000 Series – 5 A (Max) |
| CAB4006 | LD | LDC4000 Series, ITC4000 Series – 20 A (Max) |
| CON4001 | TEC | TED4015, ITC4000 Series, 17W2 |
| CON4005 | LD | LDC4000 Series, ITC4000 Series, 13W3 |

| ITEM # | \$ | £ | € | RMB | DESCRIPTION |
|-----------|-----------|----------|----------|------------|--|
| CAB400 | \$ 66.00 | £ 47.52 | € 57.42 | ¥ 526.02 | LD Current Controller Cable, 9-Pin D-Sub, 1.5 m |
| CAB420-15 | \$ 72.00 | £ 51.84 | € 62.64 | ¥ 573.84 | TEC Controller Cable, 15-Pin D-Sub, 1.5 m |
| CAB430 | \$ 120.00 | £ 86.40 | € 104.40 | ¥ 956.40 | LD and TEC Controller Cable for ITC100 and ITC8000-DS15, 1.5 m |
| CAB530 | \$ 96.00 | £ 69.12 | € 83.52 | ¥ 765.12 | ITC5000 Series to TEC & LD Driver Mounts |
| CAB4000 | \$ 65.00 | £ 46.80 | € 56.55 | ¥ 518.05 | Cable for TED4000/ITC4000, 17W2 to D-Sub-9, 5 A, 1.5 m |
| CAB4001 | \$ 170.00 | £ 122.40 | € 147.90 | ¥ 1,354.90 | TEC Controller Cable for TED4000, 20 A Max, 17W2, 1.5 m |
| CAB4005 | \$ 80.00 | £ 57.60 | € 69.60 | ¥ 637.60 | Cable for LDC4000 Series, 5 A, 13W3 to D-Sub-9, 1.5 m |
| CAB4006 | \$ 80.65 | £ 58.07 | € 70.17 | ¥ 642.78 | Cable for LDC4000 Series, 20 A, 13W3 to 13W3, 1.5 m |
| CON4001 | \$ 22.00 | £ 15.84 | € 19.14 | ¥ 175.34 | Connector Kit for 17W2 |
| CON4005 | \$ 14.50 | £ 10.44 | € 12.62 | ¥ 115.57 | Connector Kit for 13W3 |

Mounted LED Mating Connector



CON8ML-4

NEW
product

The CON8ML-4 is a female 4-pin mating connector for use with our mounted LEDs (see pages 1319 - 1321). It includes 0.5 m of 24AWG wires for customers who wish to drive our LEDs with their own controller. The connector has an M8 x 0.5 panel mount thread.

| ITEM # | \$ | £ | € | RMB | DESCRIPTION |
|----------|----------|---------|---------|----------|-----------------------------------|
| CON8ML-4 | \$ 29.15 | £ 20.99 | € 25.36 | ¥ 232.33 | Mating Connector for Mounted LEDs |

CHAPTERS ▾

Tables/
Breadboards

Mechanics

Optomechanic
Devices

Kits

Lab Supplies

SECTIONS ▾

Optics Supplies

Fiber Supplies

Electrical
Components

Lab Tools

Safety and Blackout

Screws, Nuts,
and Bolts

19" Rack Hardware

Storage