


## BNC Male Straight to BNC Male Straight Cable

### Features

- Tarnish-Resistant Brass Body
- Stress-Relieved
- Weather-Proof Cable Assemblies
- 50 Ω Impedance
- Frequency Range: DC - 4.0 GHz
- Working Voltage: 500 V (RMS)




ITEM#	\$	£	€	RMB	LENGTH
2249-C-12	\$ 13.60	£ 9.45	€ 12.10	¥ 114.90	12" (0.3 m)
2249-C-24	\$ 14.90	£ 10.35	€ 13.30	¥ 125.90	24" (0.6)
2249-C-36	\$ 17.30	£ 12.00	€ 15.40	¥ 146.10	36" (0.9 m)
2249-C-48	\$ 12.80	£ 8.85	€ 11.40	¥ 108.10	48" (1.2 m)
2249-C-60	\$ 16.00	£ 11.10	€ 14.30	¥ 135.20	60" (1.5 m)
2249-C-120	\$ 20.80	£ 14.50	€ 18.50	¥ 175.70	120" (3.0 m)

## SMA Male Straight to SMA Male Straight Cable

### Features

- 50 Ω Impedance
- Frequency Range: DC - 12.4 GHz
- Dielectric Withstanding Voltage: 750 V (RMS)
- Working Voltage: 250 V (RMS)




ITEM#	\$	£	€	RMB	LENGTH
CA2906	\$ 13.00	£ 9.00	€ 11.60	¥ 109.80	6" (0.15 m)
CA2912	\$ 13.70	£ 9.50	€ 12.20	¥ 115.70	12" (0.3 m)
CA2918	\$ 14.00	£ 9.70	€ 12.50	¥ 118.30	18" (0.5 m)
CA2924	\$ 14.30	£ 9.90	€ 12.70	¥ 120.80	24" (0.6 m)
CA2936	\$ 15.50	£ 10.75	€ 13.80	¥ 130.90	36" (0.9 m)
CA2948	\$ 16.60	£ 11.60	€ 14.80	¥ 140.20	48" (1.2 m)

## SMA Male Straight to BNC Male Straight Cable

### Features

- 50 Ω Impedance
- Frequency Range: DC - 4.0 GHz
- Dielectric Withstanding Voltage: 750 V (RMS)
- Working Voltage: 250 V (RMS)




ITEM#	\$	£	€	RMB	LENGTH
CA2806	\$ 12.20	£ 8.45	€ 10.90	¥ 103.10	6" (0.15 m)
CA2812	\$ 12.60	£ 8.75	€ 11.20	¥ 106.40	12" (0.3 m)
CA2818	\$ 13.00	£ 9.00	€ 11.60	¥ 109.80	18" (0.5 m)
CA2824	\$ 13.30	£ 9.20	€ 11.90	¥ 112.40	24" (0.6 m)
CA2836	\$ 14.30	£ 9.90	€ 12.70	¥ 120.80	36" (0.9 m)
CA2848	\$ 15.50	£ 10.75	€ 13.80	¥ 130.90	48" (1.2 m)

## SMC Female Straight to BNC Male Straight Cable

### Features

- 50 Ω Impedance
- Frequency Range: DC - 4.0 GHz
- Dielectric Withstanding Voltage: 750 V (RMS)
- Working Voltage: 250 V (RMS)



ITEM#	\$	£	€	RMB	LENGTH
CA2606	\$ 39.90	£ 27.70	€ 35.50	¥ 337.00	6" (0.1 m)
CA2612	\$ 40.20	£ 27.90	€ 35.70	¥ 339.50	12" (0.3 m)
CA2618	\$ 40.50	£ 28.10	€ 36.00	¥ 342.00	18" (0.5 m)
CA2624	\$ 40.70	£ 28.30	€ 36.20	¥ 343.70	24" (0.6 m)
CA2636	\$ 41.30	£ 28.70	€ 36.70	¥ 348.80	36" (0.9 m)
CA2648	\$ 41.80	£ 29.00	€ 37.20	¥ 353.00	48" (1.2 m)
CA2660	\$ 42.40	£ 29.40	€ 37.70	¥ 358.10	60" (1.5 m)
CA2672	\$ 42.90	£ 29.80	€ 38.10	¥ 362.30	72" (1.8 m)

Please refer to our website for complete models and drawings.