

Have you
seen our...

LED
Mounts



See page
1499


$\lambda = 525 \text{ nm}$, $P = 2.6 \text{ mW}$ LED

- Epoxy Lens, 15° Viewing Full Angle
- T-1 3/4 Package

CHARACTERISTIC (T _a = 25 °C)	MIN	TYPICAL	MAX
Peak Wavelength	520 nm	525 nm	540 nm
Optical Power @ 20 mA, CW	–	2.6 mW	–
Spectral Half Width	–	16 nm	–
Viewing Full Angle	–	15°	–
Forward Current	–	–	30 mA
Pulsed Forward Current	–	–	–
Reverse Voltage	–	–	5.0 V
Forward Voltage @ 20 mA	–	3.3 V	3.85 V
Operating Temperature	-40 °C	–	85 °C
Storage Temperature	-40 °C	–	120 °C

ITEM #	\$	£	€	RMB	DESCRIPTION
LED525E	\$ 19.00	£ 13.68	€ 16.53	¥ 151.43	Epoxy-Encased LED, 525 nm, 2.6 mW, T-1 3/4 (Qty. 5)

Sold in
Packages of 5




$\lambda = 525 \text{ nm}$, $P = 3 \text{ mW}$ LED

- Epoxy Lens, 20° Viewing Full Angle
- T-1 3/4 Package

CHARACTERISTIC (T _a = 25 °C)	MIN	TYPICAL	MAX
Peak Wavelength	515 nm	525 nm	535 nm
Optical Power @ 20 mA, CW	–	3 mW	–
Spectral Half Width	–	20 nm	–
Viewing Full Angle	–	20°	–
Forward Current	–	–	30 mA
Pulsed Forward Current	–	–	–
Reverse Voltage	–	–	5 V
Forward Voltage @ 20 mA	–	3.6 V	4.3 V
Operating Temperature	-30 °C	–	85 °C
Storage Temperature	-30 °C	–	100 °C

ITEM #	\$	£	€	RMB	DESCRIPTION
LED528E	\$ 31.00	£ 22.32	€ 26.97	¥ 247.07	Epoxy-Encased LED, 525 nm, 3 mW, T-1 3/4 (Qty. 5)

Sold in
Packages of 5



$\lambda = 525 \text{ nm}$, $P = 7.0 \text{ mW}$ LED

- Epoxy Lens, 18° Viewing Full Angle
- T-1 3/4 Package

CHARACTERISTIC (T _a = 25 °C)	MIN	TYPICAL	MAX
Peak Wavelength	520 nm	525 nm	530 nm
Optical Power @ 20 mA, CW ²	–	7.0 mW	–
Spectral Half Width	–	17.5 nm	–
Viewing Full Angle	–	18°	–
Forward Current	–	–	50 mA
Pulsed Forward Current	–	–	–
Reverse Voltage	–	–	5.0 V
Forward Voltage @ 20 mA ²	–	3.3 V	4.3 V
Operating Temperature	-30 °C	–	80 °C
Storage Temperature	-30 °C	–	100 °C

ITEM #	\$	£	€	RMB	DESCRIPTION
LED528HP	\$ 22.00	£ 15.84	€ 19.14	¥ 175.34	Epoxy-Encased LED, 525 nm, 7.0 mW, T-1 3/4 (Qty. 5)

Sold in
Packages of 5

