


## SMC Female Straight to SMC Female Straight Cable

### Features

- Impedance: 50Ω
- Frequency Range: DC - 12.4GHz
- Dielectric Withstanding Voltage: 750V (RMS)
- Working Voltage: 250V (RMS)




ITEM#	\$	£	€	RMB	LENGTH
CA2706	\$ 39.70	£ 25.00	€ 36.90	¥ 379.10	6" (152mm)
CA2712	\$ 40.40	£ 25.50	€ 37.60	¥ 385.80	12" (304mm)
CA2718	\$ 41.20	£ 26.00	€ 38.30	¥ 393.50	18" (457mm)
CA2724	\$ 42.00	£ 26.50	€ 39.10	¥ 401.10	24" (609mm)
CA2736	\$ 42.70	£ 26.90	€ 39.70	¥ 407.80	36" (914mm)
CA2748	\$ 43.50	£ 27.40	€ 40.50	¥ 415.40	48" (1219mm)
CA2760	\$ 45.10	£ 28.40	€ 41.90	¥ 430.70	60" (1524mm)

## USB 2.0A Male to USB 2.0A Female Cable

### Features

- USB 2.0
- Hi-Speed 480Mbps Transmission
- 28 Gauge Conductor




### USB Cable

ITEM#	\$	£	€	RMB	LENGTH
USB-C-18	\$ 5.00	£ 3.20	€ 4.70	¥ 47.80	18" (0.46m)
USB-C-36	\$ 5.80	£ 3.70	€ 5.40	¥ 55.40	36" (0.91m)
USB-C-72	\$ 6.70	£ 4.20	€ 6.20	¥ 64.00	72" (1.83m)
USB-C-180	\$ 8.30	£ 5.20	€ 7.70	¥ 79.30	180" (4.57m)

## USB 2.0A Male to USB 2.0 MiniB Cable

### Features



- USB 2.0
- RoHS Compliant
- Multiple Lengths Available



### USB Cable

ITEM#	\$	£	€	RMB	LENGTH
USB-AB-36	\$ 7.00	£ 4.40	€ 6.50	¥ 66.90	36" (0.91m)
USB-AB-72	\$ 7.75	£ 4.90	€ 7.20	¥ 74.00	72" (1.83m)

## Banana Patch Cords



### Features

- Hands Free Use in Controlled Environments: 5000VDC Max.
- Handheld Use: 30VAC/60DC
- Stackable

### Patch Cords (Red)

ITEM#	\$	£	€	RMB	LENGTH
T13122	\$ 6.40	£ 4.00	€ 6.00	¥ 61.10	12" (0.31m)
T13242	\$ 6.80	£ 4.30	€ 6.30	¥ 64.90	24" (0.61m)

### Patch Cords (Black)

ITEM#	\$	£	€	RMB	LENGTH
T13120	\$ 6.40	£ 4.00	€ 6.00	¥ 61.10	12" (0.31m)
T13240	\$ 6.80	£ 4.30	€ 6.30	¥ 64.90	24" (0.61m)

## Cable Racks

### Features

- Organize Loose Cables and Electrical Patch Cords
- Model T1508 is Great for Fiber Optic Cables
- Easy Mounting



ITEM#	\$	£	€	RMB	DESCRIPTION
T1508	\$ 12.00	£ 7.60	€ 11.20	¥ 114.60	Narrow Slots For Use with BNC and SMA Cables
T2708	\$ 12.40	£ 7.80	€ 11.50	¥ 118.40	Wide Slots For Use with Power Cords and Large Cables