


White Light, P = 1.0 mW LED

- Epoxy Lens, 15° Viewing Full Angle
- T-1 3/4 Package

Sold in
Packages of 5



CHARACTERISTIC (T _a = 25 °C)	MIN	TYP.	MAX
Optical Power @ 20 mA, CW	–	1.0 mW	2.6 mW
Viewing Full Angle	–	15°	–
Forward Current	–	–	30 mA
Reverse Voltage	–	–	5.0 V
Forward Voltage @ 20 mA	–	3.2 V	3.6 V
Operating Temperature	-30 °C	–	80 °C
Storage Temperature	-40 °C	–	100 °C



ITEM#	\$	£	€	RMB	DESCRIPTION
LEDWE-15	\$ 9.00	£ 6.25	€ 8.00	¥ 76.00	Epoxy Encased White Light LED, 1.0 mW, T-1 3/4 (Qty. 5)


White Light, P = 2.6 mW LED

- Epoxy Lens, 10° Viewing Half Angle
- T-1 3/4 Package

Sold in
Packages of 5



CHARACTERISTIC (T _a = 25 °C)	MIN	TYP.	MAX
Optical Power @ 20 mA, CW	–	2.6 mW	–
Viewing Full Angle	–	20°	–
Forward Current	–	–	30 mA
Pulsed Forward Current	–	–	80 mA
Reverse Voltage	–	–	5.0 V
Forward Voltage @ 20 mA	–	3.2 V	3.6 V
Operating Temperature	-30 °C	–	80 °C
Storage Temperature	-40 °C	–	100 °C



ITEM#	\$	£	€	RMB	DESCRIPTION
LEDWE-10	\$ 10.00	£ 6.95	€ 8.90	¥ 84.50	Epoxy-Encased White Light LED, 2.6 mW, T-1 3/4 (Qty. 5)


White Light, P = 3.7 mW LED

- Epoxy Lens, 50° Viewing Full Angle
- T-1 3/4 Package

Sold in
Packages of 5



CHARACTERISTIC (T _a = 25 °C)	MIN	TYP.	MAX
Optical Power @ 20 mA, CW	–	3.7 mW	–
Viewing Full Angle	–	50°	–
Forward Current	–	–	30 mA
Pulsed Forward Current	–	–	150 mA
Reverse Voltage	–	–	5.0 V
Forward Voltage @ 20 mA	–	3.1 V	3.6 V
Operating Temperature	-40 °C	–	80 °C
Storage Temperature	-40 °C	–	85 °C



ITEM#	\$	£	€	RMB	DESCRIPTION
LEDWE-50	\$ 5.75	£ 4.00	€ 5.20	¥ 48.60	Epoxy-Encased White Light LED, 3.7 mW, T-1 3/4 (Qty. 5)