



DIVERSIFIED
TESTING LABORATORIES, INC.
WORLDWIDE SERVICE

“We Test Per Your Request”

336 WEST FRONT STREET
P.O. BOX 4004
BURLINGTON, NORTH CAROLINA 27215
PHONE (336) 227-7710 • FAX (336) 227-1175
www.diversifiedtestinglabs.com

February 20, 2018

THORLABS LTD.
1 Saint Thomas Place
Cambridgeshire Business Park
Ely, Cambridgeshire CB7 4EX
United Kingdom

Reference: Laboratory Test Report
Lab Identification No. 29271
Invoice No. 60461

One (1) fabric sample, identified as **RIVERTEX 500-FR PU**, was received and tested in accordance with the National Fire Protection Association No. 701, "Standard Methods of Fire Tests for Flame Propagation of Textiles and Films, 2015 Edition, (Test 1, Small Scale)". **The sample was tested after 72 hours of leaching.** The results are as follows:

| <u>Specimen Number</u> | <u>Test Results</u> | |
|------------------------|------------------------------------|---------------------------------|
| | <u>Residual Flame</u> (seconds) | <u>Weight Loss</u> (percent) |
| 1 | 0.0 | 17.76 |
| 2 | 0.0 | 20.86 |
| 3 | 0.0 | 16.62 |
| 4 | 0.0 | 25.70 |
| 5 | 0.0 | 22.61 |
| 6 | 0.0 | 23.19 |
| 7 | 0.0 | 29.04 |
| 8 | 0.0 | 30.56 |
| 9 | 0.0 | 29.81 |
| <u>10</u> | <u>0.0</u> | <u>29.16</u> |
| AVG | 0.0 | 24.53 |

The sample submitted **meets** the minimum requirements of the above standard. The average percent weight loss cannot exceed 40% and the weight loss of individual specimens cannot exceed mean value plus three standard deviations. The average residual flame cannot exceed 2.0 seconds.

If there are any questions or when we can be of further assistance, please let us know.

Sincerely,

Brian S. Dement

BSD/mr

