

FINAL INSPECTION REPORT

1x2 50:50 PM Narrowband Coupler

Item #: PN1550R5A1
SN: T008180

Center Wavelength: 1550 nm
Coupling Ratio Specification
Signal Output: 46 % - 54 %
Tap Output: 46 % - 54 %
Bandwidth: ± 15 nm
Maximum Optical Power^a
With Connectors or Bare Fiber: 1 W
Spliced: 5 W
Fiber Type: Corning PR PM 15-U25D-H

Test Data ^b	
Excess Loss ^c	≤ 0.5 dB
Input-Output Path	White (Input) – White (Signal Output)
Coupling Ratio ^d	48.4 %
Insertion Loss ^e	3.16 dB
PER ^f	26.4 dB
Input-Output Path	White (Input) – Red (Tap Output)
Coupling Ratio ^d	51.6 %
Insertion Loss ^e	2.88 dB
PER ^f	23.1 dB

- a. Specifies the maximum power allowed through the component. Performance and reliability under high power conditions must be determined within the user's setup.
- b. All values are measured at room temperature without connectors through the white input port.
- c. Ratio of the input optical power to the total optical power from all output ports. It is measured at the center wavelength.
- d. Does not include losses, as this is a measurement of the output power distribution only.
- e. Includes both the split of the power between the two outputs, as well as any optical losses in the coupler.
- f. Measured with a slow axis launch at room temperature with connectors at the center wavelength through the white input port.